

Advanced Test Equipment Rentals www.atecorp.com 800-404-ATEC (2832)

((++-))

Sound Level Meters for Safety & Health Professionals

SoundTrack LxT®

A Real Breakthrough in Occupational Noise Analysis

Highlights

- Simple Operation with just one hand!
- 30 hours operation using AA lithium batteries
- Large, bright, high-contrast LCD Screen
- 1/1 and 1/3 octave digital filters
- Extremely rugged compact and lightweight
- Available in Class 1 or Class 2
- Multi-language for global compatibility



Multiple Measurements from one Sampling Session

- Real-time broadband display
- Real-time octave filters
- Real-time 1/3 octave filters
- Leq (average w/ 3 dB exchange rate)
- TWA
- Logging

A Revolutionary Approach to Workplace Noise Sampling

Over the years, various types of Sound Level and Octave Band Meters have been used by Industrial Hygienists and Safety Professionals for monitoring workplace noise, most requiring significant operator training and producing varying degrees of effectiveness. At Larson Davis, we believe this is because until now, Sound Level Meters were designed primarily for use by Acoustical Engineers, not for Safety and Health professionals.

Lmax

Lpeak

calculations

Multiple dose and exposure

Digital voice annotation

Time stamping of relevant metrics

The SoundTrack LxT[®] Sound Level Meter was developed to meet the unique needs of those involved in workplace noise exposure assessment and plant noise surveys. It is fully compliant with IEC and ANSI standards for Class 1 or Class 2 sound level meters. In addition, LXT files are fully compatible with the ISO 9612:2009 measurement strategies for task or job-based measurements.

With its sleek ergonomic design to its exceptional exposure data presentations, the SoundTrack $LxT^{(B)}$ is the perfect tool for gathering, analyzing, and presenting detailed noise environment data quickly, easily and concisely. New and better ways to organize your sampling methodology and annotate noise survey data save incredible amounts of time and provide better results – all at a price that won't consume your entire instrumentation budget.



SoundTrack LxT®

Easy to Use, Yet Powerful!

With its superior ergonomics and rugged compact design, SoundTrack LxT[®] allows you to capture the data you need while keeping one hand free – invaluable for juggling multiple tasks in hard-to reach locations. Once a test starts, LxT automatically performs all the necessary calculations of workplace exposure - to multiple compliance standards. With the ability to 'hide' display screens that are not relevant to your sampling strategy, the LxT is configurable for maximum utility and ease-of use. Add in the "Store when Stable (Leq)" feature and selective keypad lockout, and you can comfortably hand off the SoundTrack LxT[®] to minimally trained technicians with assurance of a positive outcome. No more skipped locations, questionable results and missing data points.

Digital Voice Annotation

Now you can record your own observations about the environment, the worker and tasks performed, or even whether proper hearing protection is worn – all at the push of a button, using the Digital Voice Note Recording option and included headset microphone. At the end of the day, recorded notes can be played back right from your PC – they are digitally stored with related noise data and exposure calculations for future reference.

Available Real-Time Octave Band Frequency Analysis

With optional 1/1 or 1/3 Real-Time Octave Band Frequency Analysis, the SoundTrack LxT[®] quickly captures frequency band data, because all Octave (or 1/3 Octave) measurements are performed simultaneously. No more tedious "stepping through" each Octave Band, as in the past – all data are captured from virtually the same point in time; which is vital for maximum accuracy in a varying noise environment. What's more, you'll save significant amounts of time performing Octave Band measurements, which are an important part of determining effectiveness of Engineering Controls or selecting proper hearing protection devices (HPD's).

SoundTrack LxT® Shown with 1/3 Octave Frequency Analysis

💿 0:00:00.0 🛷 🗖	💿 0:00:58.1 🔗 🕨	💿 0:02:43.8 🛷 🕨	🕙 0:03:22.4 🛷 🔳
Control Panel		LxT_Data	LxT_Data
	Live Overall Session Log C	Live Overall Session Log C	Session Log Current
	LAeq dB 🖾 🗋	OSHA-1	Exceedances
Data Calibrate Explorer		TWA(8.0) 30.6 dB	LAF > 85.0 dB 20 0:00:15.1
0	59.7	ProjTWA 67.9 dB Lep,d 57.4 dB	LAF > 115.0 dB 0:00:00.0
Setup Manager Voice Recorder	LAF > 85.0 dB 0.0 %	DOSE 0.03 % ProjDose 4.64 %	LZpeak > 135.0 dB 0:00:00.0
** ?	LAFmax 80.8 dB	Weighting A Exchange Rate 5 dB	LZpeak > 137.0 dB 0:00:00.0
System About	LZpeak(max) 105.1 dB Run Time: 0:00:58.1	Threshold 90.0 dB Criterion 8.0 h, 90.0 dB	LZpeak > 140.0 dB 0:00:00.0
Properties	Pause Time: 0:00:00.0	Run Time: 0:02:43.8	Run Time: 0:03:22.4
🔺 Close 🗨	🔹 Menu 🕨	🖌 Menu 🕨	🔹 Menu
Familiar Controls for Ease-of-use	Large Numeric Display	(2) Virtual Noise Dosimeters	User Selectable Threshold Counters



2

Larson Davis

Sound Level Meters for Safety & Health Professionals





Document - Manage - Examine - Present

* Vers 6.10

ARSON DAVIS


Generate Clear, Concise Reports with Blaze® Software

Blaze[®] Software is an invaluable tool for generating the types of data reports and presentations you'll be proud to share with your colleagues, your workforce, and management. Color-rich graphic summary reports provide a picture of the noise environment with only the most relevant numeric data values, enabling everyone

to quickly understand the nature of the noise exposure. With super-fast USB connection, you'll go from measurement to finished report in seconds. By accessing Blaze®'s more advanced features, you will be able to provide higher-level analysis of the noise environment with as much additional annotation as needed. Copy and paste functions allow for inclusion of data into other report formats, and – for the most advanced users and research teams – a simple export function allows instant and automatic interface to popular spreadsheet programs.



Whether you'd like a one-page illustrated compliance report or a detailed breakdown of noise data, Blaze[®] delivers effortlessly – and supports other Larson Davis products like Spark[®] Noise Dosimeters and the HVM100 Vibration Exposure monitoring system. And, with our "no-hassle" software agreement, you'll never be hit with recurring licensing fees or other additional costs, should you choose to install Blaze[®] on other PC's or laptops within your organization.



Sound Level Meters for Safety & Health Professionals

	, orgini	LxT1	hting: A, C, & Z, Octa LxT2		
				LxT1L with optional LOW RANGE Pre-amp	LxT2L with optional LOW RANGE Pre-amp
Measurement	Α	38 to 140 dB SPL	37 to 140 dB SPL	27 to 118 dB SPL	29 to 121 dB SPL
Range	C	37 to 140 dB SPL	37 to 140 dB SPL	29 to 118 dB SPL	32 to 121 dB SPL
	Z	42 to 140 dB SPL	42 to 140 dB SPL	34 to 118 dB SPL	36 to 121 dB SPL
SPL maximum level		140 dB SPL	140 dB SPL	118 dB SPL	121 dB SPL
Peak level		143 dB	143 dB	121 dB	124 dB
SPL, Leq, TWA (2), Lmi Counters (3); (2 RMS, 3 Data Storage / Flash Data Storage: 2	B Peak) / Co i	nmunicatio		se (2), Lep,d, E, E8, E4	10, SEA, Ln (6), Event
Communication to PC					
bright white LED backli Keypad: Silicone elast and 5 navigation keys			tactile feedback, 4 deo	dicated function keys,	, 3 context soft-keys,
Power					
Internal: 4 AA cells, 1					
Internal: 4 AA cells, 1 External: 5.0 VDC ±5%	%, 500	mA maximum, USB	powered	n cells) depending on	
Internal: 4 AA cells, 1 External: 5.0 VDC ±5% Battery life: Approxim	%, 500i nately 2	mA maximum, USB 22 hours (alkaline c	powered	n cells), depending on	usage
Internal: 4 AA cells, 1 External: 5.0 VDC ±59 Battery life: Approxim Physical Char Dimensions: 8.8" L x and micr	%, 500 nately 2 acte 2.8" W rophon	mA maximum, USB 22 hours (alkaline c eristics / x 1.6" D (22.4 cm : e	powered ells), 30 Hours (lithiun x 7.1 cm x 4.1 cm), 11	.5" L (29.2 cm) with p	0
Internal: 4 AA cells, 1 External: 5.0 VDC ±5% Battery life: Approxim Physical Char Dimensions: 8.8" L x. and micr Weight: 1.0 lbs (471 g	%, 500i nately 2 acte 2.8″ W rophon I), 1.1 II	mA maximum, USB 22 hours (alkaline c eristics / x 1.6" D (22.4 cm : e	powered ells), 30 Hours (lithiun x 7.1 cm x 4.1 cm), 11	.5" L (29.2 cm) with p	0
Internal: 4 AA cells, 1 External: 5.0 VDC ±5% Battery life: Approxim Physical Char Dimensions: 8.8" L x and micr Weight: 1.0 lbs (471 g Environmental	%, 500 nately 2 acte 2.8" W rophon I), 1.1 II	mA maximum, USB 22 hours (alkaline c eristics / x 1.6" D (22.4 cm s e bs (513 g) with prea	powered ells), 30 Hours (lithiun x 7.1 cm x 4.1 cm), 11 amplifier and micropho	.5" L (29.2 cm) with p	0
Internal: 4 AA cells, 1 External: 5.0 VDC ±5% Battery life: Approxim Physical Char Dimensions: 8.8" L x and micr Weight: 1.0 lbs (471 g Environmental Operating temperatu	%, 500 nately 2 a cte 2.8" W rophon I), 1.1 II I I ure: 14	mA maximum, USB 22 hours (alkaline c eristics / x 1.6" D (22.4 cm : e bs (513 g) with prea to 122 °F (-10 to 50	powered ells), 30 Hours (lithiun x 7.1 cm x 4.1 cm), 11 amplifier and micropho D °C)	.5" L (29.2 cm) with p	0
Internal: 4 AA cells, 1 External: 5.0 VDC ±5% Battery life: Approxim Physical Char Dimensions: 8.8" L x and micr Weight: 1.0 lbs (471 g Environmental Operating temperature	%, 500 nately 2 2.8" W rophon I), 1.1 II I ure: 14 e: -22 t	mA maximum, USB 22 hours (alkaline c eristics / x 1.6" D (22.4 cm : e bs (513 g) with prea to 122 °F (-10 to 50 to 140 °F (-30 to 60	powered ells), 30 Hours (lithiun x 7.1 cm x 4.1 cm), 11 amplifier and micropho D °C)	.5" L (29.2 cm) with p	0
Internal: 4 AA cells, 1 External: 5.0 VDC ±5% Battery life: Approxim Physical Char Dimensions: 8.8" L x and micr Weight: 1.0 lbs (471 g Environmental Operating temperature Humidity: up to 95% r	%, 500 nately 2 acte 2.8" W rophon 1), 1.1 II 1 nre: 14 a: -22 f non-co	mA maximum, USB 22 hours (alkaline c eristics / x 1.6" D (22.4 cm : e bs (513 g) with prea to 122 °F (-10 to 50 to 140 °F (-30 to 60 ndensing	powered ells), 30 Hours (lithiun x 7.1 cm x 4.1 cm), 11 amplifier and micropho D °C)	.5" L (29.2 cm) with p	0
Internal: 4 AA cells, 1 External: 5.0 VDC ±59 Battery life: Approxim Physical Char Dimensions: 8.8" L x and micr Weight: 1.0 lbs (471 g Environmental Operating temperature Humidity: up to 95% r International Protect	%, 500 nately 2 a cte 2.8" W rophon I), 1.1 II I I I I I I I I I I I I I I I I I I	mA maximum, USB 22 hours (alkaline c eristics / x 1.6" D (22.4 cm : e bs (513 g) with prea to 122 °F (-10 to 50 to 140 °F (-30 to 60 ndensing ating: IP 54	powered ells), 30 Hours (lithiun x 7.1 cm x 4.1 cm), 11 amplifier and micropho D °C)	.5" L (29.2 cm) with p	0
Internal: 4 AA cells, 1 External: 5.0 VDC ±59 Battery life: Approxim Physical Char Dimensions: 8.8" L x and mice Weight: 1.0 lbs (471 g Environmental Operating temperature Humidity: up to 95% of International Protect Standards Con	%, 500 nately 2 acte 2.8" W rophon (), 1.1 II (), 1.1 I	mA maximum, USB 22 hours (alkaline c eristics / x 1.6" D (22.4 cm) e bs (513 g) with prea to 122 °F (-10 to 50 to 140 °F (-30 to 60 ndensing ating: IP 54 ance	powered ells), 30 Hours (lithiun x 7.1 cm x 4.1 cm), 11 amplifier and micropho D °C) °C)	5" L (29.2 cm) with p	0
Internal: 4 AA cells, 1 External: 5.0 VDC ±59 Battery life: Approxim Physical Char Dimensions: 8.8" L x and micr Weight: 1.0 lbs (471 g Environmental Operating temperature Humidity: up to 95% r International Protect	%, 500 nately 2 a cte 2.8" W rophon 1), 1.1 II 1 ure: 14 2: -22 f non-co tion R 5001), S	mA maximum, USB 22 hours (alkaline c eristics (x 1.6" D (22.4 cm) e bs (513 g) with prea to 122 °F (-10 to 50 to 140 °F (-30 to 60 ndensing ating: IP 54 ance I.43-1997 (R 2002),	powered ells), 30 Hours (lithiun x 7.1 cm x 4.1 cm), 11 amplifier and micropho 0 °C) °C) S1.25-1991 (R 2007),	5" L (29.2 cm) with p	0



Options and Accessories				
Firmware Options				
LXT-LOG	Time History Data Logging			
LXT-HSLOG	High Speed Logging Option (to 100ms)			
LXT-ENV	Measurement History (intervals)			
LXT-CN	Community Noise, Ldn & Lden			
LXT-DVA	Digital Voice Annotation			
LXT-OB1	1/1 Octave Real Time Filters			
LXT-OB3	1/1 and 1/3 Octave Real Time Filters			
Accessories				
LXT-ACC	Type 1 Accessory Kit - Pelican case, CAL200 calibrator, PC cable, AC adapter, windscreen and Utility Software			
LXT-ACC1	Type 2 Accessory Kit - same as above with CAL150 Type 2 calibrator			
LXT-CCS	Hard Shell Pelican Carrying Case			
CAL150	Type 2 Microphone Calibrator			
CAL200	Type 1 Microphone Calibrator			
SWW-DNA	Advanced Analysis Software			
SWW-DNA-LXT	DNA Instrument Driver for Model LxT			
SWW-BLAZE-LXT	Industrial Hygiene Software for Model LxT			
Special LxT Co	onfigurations			
LXT1-QPR	High Decibel Configuration for Model LxT - includes 1/4" microphone to measure >160dB			
LXT1-NFR-PK1	Type 1 Noise N'Forcer Kit - includes portable printer			
LXT2-NFR-PK2	Type 2 Noise N'Forcer Kit - includes portable printer			

Complementary Industrial Hygiene Products

Noise Dosimeters

- ✓ Compact
- Rugged
- ✓ 100 Hour Battery Life



Vibration Exposure Monitors

- ✓ Hand-Arm per ISO 5349, ANSI S2.7
- ✓ Whole-Body per ISO 2631
- Complete with sensors and easy to use

Remember, all of these instruments are supported by Blaze[®] Software.



3425 Walden Avenue, Depew, NY 14043-2495 USA

Phone 716-926-8243 • Toll-Free in USA 888-258-3222 • Fax 716-926-8215

E-mail sales@larsondavis.com • Web Site www.larsondavis.com

ISO 9001 CERTIFIED

© 2013 PCB Group, Inc. In the interest of constant product improvement, specifications are subject to change without notice. PCB, and ICP are registered trademarks of PCB Group Inc., SoundTrack LXT, Spark and Blaze are registered trademarks of PCB Piezotronics, Inc. HVManager is a trademark of PCB Piezotronics, Inc. All other trademarks are property of their respective owners.

LD-SoundTrackLxT-0613

Printed in U.S.A.

For environmental noise monitoring and building acoustics, **Larson Davis** offers a full line of instruments, accessories and software. For personal noise and vibration exposure monitoring, Larson Davis complements this with sound level meters, personal noise dosimeters, human vibration meters, audiometric calibration systems and hearing conservation programs.

> Visit www.larsondavis.com to locate your nearest sales office