



Advanced Test Equipment Rentals
www.atecorp.com 800-404-ATEC (2832)

Automated Loss Test Set

FOT-920 MaxTester



- FasTesT—automated bidirectional loss testing
- Optical return loss testing
- Simultaneous talking, testing and locating
- Ultra-High-Power™ power meter



Fiber-optic T&M,
monitoring, manufacturing
and assembly solutions



Maximum Versatility

The FOT-920 MaxTester Automated Loss Test Set is the unit of choice for field technicians in network installation and maintenance. This unit integrates a fully automated bidirectional loss test set (OLTS), a light source and the Ultra-High-Power™ power meter with useful options, including a full-duplex digital talk set, visual fault locator and optical return loss test set, to create versatile combinations.

High-Fiber-Count Installation

The FOT-920 gives you the edge when it comes to high-fiber-count installation. First, when doing a large volume of testing, the return on your investment takes less than a year. Second, the FOT-920 reduces the time you spend testing, training and in the field, making it ideal for outside plant applications.

OC-48 and OC-192 Systems

Due to their high modulation rates, lasers used to transmit at OC-48 and OC-192 speeds are highly sensitive to backreflection. When installing networks designated to transmit at these speeds, measuring backreflection is a must to ensure proper stability of the lasers and their central wavelength.

Maximize your testing capacity with the FOT-920 MaxTester.



Key Benefits

- Automated dual-wavelength bidirectional loss testing on one connector in less than 30 seconds
- Storage of up to 512 fiber records
- Message-exchange capability
- Backreflection capacity ideal for OC-48 and OC-192 systems
- Power meter with up to 35 dBm capability
- Three-way powering: NiMH and 9V batteries; AC adapter/charger

Detector port

Compatible with almost every connector on the market. Manually perform power and loss testing efficiently. Accurately measure power up to +35 dBm with the Ultra-High-Power™ models.

FasTesT port

Transmit one or two wavelengths through a single port. Also, use this port to perform ORL measurements, to send messages and to use the light source feature.

RS-232 interface

Transfer data to a PC or to a portable printer.

VFL

Built-in 650 nm visual fault location.

Talk set port

For full-duplex voice communication.

Headset port

For hands-free talk set operation.



Step Up to the Ultra-High-Power™ Models (FOT-923X)

Networks today need high power. The networks of tomorrow will require even more. This growing demand for power is driven by the stress being placed on fiber-optic networks.

Directly measure the absolute power of high-output signals in the field with the FOT-923X's Ultra-High-Power™ capabilities. Accurately measure signals with power levels as high as +35 dBm, without neglecting those at the lower end of the dBm range. The Ultra-High-Power™ models are the complete solution for advanced networks.

Leave Nothing to Chance

There is no substitute for practicing good laser safety. When handling high power, always take necessary precautions.

The All-in-One Unit

Bidirectional, Dual-Wavelength Testing and Professional Reports

EXFO understands that your time is valuable; that's why the FOT-920 features the patented FasTesT system. FasTesT automatically measures single-fiber loss in both directions, at two wavelengths, in less than 30 seconds. To speed up the reporting process, the FOT-920 stores all test results in its non-volatile memory; later, you can file test data according to your own cable identification scheme. Create more extensive reports, including user and test location information, with ToolBox 6 software (included). Download, print or store results on a computer hard drive.

ToolBox 6

Optical Return Loss (ORL)

With widespread use of OC-48 and OC-192 transmission systems, bandwidth is essential. Flawless operation of high-data-rate systems depends on measurement and control of backreflection or optical return loss (ORL).

ORL can affect transmissions by


- Destabilizing DFB laser sources
- Interfering with high-frequency analog signals
- Increasing the bit error rate in high-frequency digital signals

Simply measure ORL with the FOT-920 using the optical continuous wave reflectometer (OCWR) method.

Talk Set Communication and Visual Fault Location


Coordinate end-to-end testing between remote sites with a fiber-optic talk set. The FOT-920 features an optional, full-duplex digital talk set for crystal-clear voice transmission. If the talk set cannot be used, the unit can send preset or preprogrammed messages via the fiber under test.

Perform end-to-end identification or pinpoint breaks, bends, faulty connectors, splices and other causes of signal loss over a distance of up to 5 km. At the exact fault location, the visual fault locator (VFL) emits a red glow that is visible through most yellow-jacketed fibers.



Maximizing Testing Efficiency

The FOT-920 MaxTester is a compact, portable test tool that stands up to virtually any field environment. It features a splashproof casing, durable shoulder strap and long-life rechargeable battery. The backlit alphanumeric display quickly and easily shows you results and messages under any light conditions.



00/03/10 03:17	
	1550 1625
A+B	-00.38 -00.65
B+A	-00.41 -00.70
AUG	-00.39 -00.68
REF	
A	-01.75 -03.34
B	-02.12 -04.44
MARGIN	STORE
REDO TEST	CANCEL FASTEST

With L-band transmission on the rise, testing at 1625 nm is now a must! (Testing at this wavelength provides worst-case attenuation for the L-band.)

99/04/10 13:00	
1 : NÄCHSTES KABEL	
2 : NÄCHSTE FASER	
3 : PROBL.- RUF UNS AN	
4 : PROBL.- 5 MIN. WARTEN	
HAUPT-MENU	SENDEN
	MENU

Two languages are installed: English plus your choice of French, Spanish, German or Czech.

96/01/06 12:02	
1 : GO TO NEXT CABLE	
2 : GO TO NEXT FIBER	
3 : TROUBLE - CALL ME	
4 : TROUBLE - WAIT 5 MIN.	
MAIN MENU	SEND
	PREV MENU

To speed up testing procedures, choose from several preprogrammed messages to send to a test partner.

00/03/10 03:07	
λ	THRESHOLD
1550	-01.70 dB
1625	-10.12 dB
+BOTH ENABLED	
PREV.	LANG./ TIME
	AUTO-OFF
	FASTEST SETUP

Configure Pass/Fail thresholds for each wavelength. If results exceed thresholds, an alarm and a highlighted value on the screen will notify you.

96/01/06 18:22	
DATE:	96/10/29
TIME:	18:29
CABLE:	CBL00002
FIBER:	FBR12345
PRESS FasTesT TO CONTINUE	
VIEW RESULTS	TAKE REF.
	IDENTIFY
	CANCEL FASTEST

Organize test results using alphanumeric identifiers that directly reflect your cable and fiber identification system.

00/03/10 00:34	
AUTO-OFF	
ENABLED	
PREV.	LANG./ TIME
	AUTO-OFF
	FASTEST SETUP

Save battery operating time. The Auto-Off function shuts the unit down after 15 minutes of inactivity.

96/01/06 18:01	
LOOPBACK	
CONNECT AND OK	
OK	CANCEL

Set up your references from different sites by using the loopback reference method.

Wide-Ranging Compatibility

FasTest, a rapid, automated dual-wavelength, bidirectional loss test, can be carried out with the following products: the FOT-920 MaxTester, an automated loss/return loss test set, and the FTB-3920 MultiTest Module. Obtain crystal-clear voice communication using any two of the following products: talk set options for the FOT-920 MaxTester, the FTB-1400 and the FTB-3920 MultiTest Modules, as well as the VCS-20A Multi-Function Fiber-Optic Talk Set. The FCD-10B Clip-On Device can be attached to a non-terminated fiber for communication between two talk sets.



Data Management

With increasing fiber deployment in Telco and CATV networks, busy fiber installation companies sometimes hire subcontractors to perform installation jobs. But subcontractors need to provide test documentation to show that a job meets specifications.


Now, subcontractors who use the FOT-920 can produce quality documentation efficiently. Thanks to the data logging and management features of the FOT-920, users can archive results and download information through the RS-232 port to a PC for professional analysis and report generation.

MultiTest Report

Job ID	Job Info	Passes	NEW/OLD
1000	Job 2704	1	NEW/OLD
Customer	McLaren	Operator	Operator
Contract	McLaren	Device S	2.5
Site Code	10000000	Time	1:00
Output File		Custom File	FILE1.txt

Case ID	Case Name	Case Type	Case ID	Case Name	Case Type
Case ID: 00000000	SALPOPS	00000000	Case ID: 00000000	00000000	00000000
Case Name: 00000000	00000000	00000000	Case Name: 00000000	00000000	00000000
Case Type: 00000000	00000000	00000000	Case Type: 00000000	00000000	00000000

Fiber	A-W	B-W	Loss	A-W	B-W	Loss
FIBER0001	1.00	1.00	0.00	1.00	1.00	0.00
FIBER0002	1.00	1.00	0.00	1.00	1.00	0.00
FIBER0003	1.00	1.00	0.00	1.00	1.00	0.00
FIBER0004	1.00	1.00	0.00	1.00	1.00	0.00
FIBER0005	1.00	1.00	0.00	1.00	1.00	0.00
FIBER0006	1.00	1.00	0.00	1.00	1.00	0.00
FIBER0007	1.00	1.00	0.00	1.00	1.00	0.00
FIBER0008	1.00	1.00	0.00	1.00	1.00	0.00
FIBER0009	1.00	1.00	0.00	1.00	1.00	0.00
FIBER0010	1.00	1.00	0.00	1.00	1.00	0.00
Average	1.00	1.00	0.00	1.00	1.00	0.00



Our ToolBox 6 software will automatically set up test data in an easy-to-read and well-organized table.

Once the data has been downloaded, it is possible to write up customized, detailed reports for any job.

The Complete Test Kit Solution

The FOT-920 MaxTester is part of EXFO's Test Kit series for all users of test and measurement instruments. These test kits are ideal for singlemode and multimode applications. All EXFO fiber-optic test kits contain accessories such as cleaning kits, AC adapters, test jumpers and fiber-optic adapters. Test equipment and accessories are stored in a convenient carrying case. Consult EXFO's Fiber-Optic Test Kit brochure for more information about the choice of test kits available.

Key Test Tools



Fiber-Optic Microscope (FOMS)
Examine connector ferrule endfaces. Choose magnification of 200x or 400x.



Visual Fault Locator (FLS-240 series)
Check system continuity. The VFL emits a visible light (635 nm) through connection flaws and cracked cables.



Live Fiber Detector (LFD-200)
Check for traffic, optical tones and continuous signals without disrupting communication, and display power levels.



Reel Cleaner (FCC-02R)
Clean connector endfaces.



OC-KIT-100

- FOT-920: high-power germanium detector, and return loss option, 1310/1550 nm source, universal adapter
- FLS-240 (635 nm model)
- FOMS Microscope (200x or 400x)
- LFD-200 Live Fiber Detector
- Connector cleaner

OC-KIT-134

- FOT-920: high-power germanium detector, and return loss option, 1550/1625 nm source, universal adapter
- FLS-240 (635 nm model)
- FOMS Microscope (200x or 400x)
- LFD-200 Live Fiber Detector
- Connector cleaner

OC-KIT-200

- FOT-920: high-power germanium detector, and return loss option, 1310/1550 nm source, talk set 1310 nm, VFL
- FLS-240 (635 nm model)
- FOMS Microscope (400x)
- LFD-200 Live Fiber Detector
- Connector cleaner

OC-KIT-400

- Two FOT-920 high-power germanium detectors, and return loss option, 1550/1625 nm source, universal adapter (talk set 1550 nm, VFL)

Specifications ¹

Power Meter	FOT-922	FOT-922X	FOT-923	FOT-923X			
Detector type	Ge (2mm)	GeX (2mm)	InGaAs (2mm)	InGaAs Ultra-High-Power			
Power level	–	–	–	P1	P2		
Measurement range ² (dBm)	10 to –68	21 to –60	4 to –70	28 to –45	35 to –45		
Uncertainty ^{3,4} (%)	± 5	± 5	± 5	± 6 ⁵	± 6.5 ⁶		
Wavelength range (nm)	780 to 1625	780 to 1625	840 to 1650	980 to 1625	980 to 1625		
Resolution ³ (dB)	0.01	0.01	0.01	0.01	0.01		
Linearity ^{2,3,4} (dB)	± 0.06	± 0.06	± 0.06	± 0.1 ⁷	± 0.1 ⁷		
FasTesT/Source/ORL⁴	–12C	–12D	–23B	–23BL	–34BL	–BR23BL	–BR34BL
Emitter type	LED	LED	LED	laser	laser	laser	laser
Wavelengths (nm)	850 ± 30/ 1300 ± 30	850 ± 30/ 1300 ± 30	1310 ± 25/ 1550 ± 25	1310 ± 25/ 1550 ± 25	1550 ± 25/ 1625 ± 25	1310 ± 25/ 1550 ± 25	1550 ± 25/ 1625 ± 25
Output power (dBm)	≥ –23/–19	≥ –20/–21	≥ –25/–30	≥ –3.5/–5.5	≥ –5.5/–5.5	≥ –5/–7	≥ –7/–7
Spectral width ⁸ (nm)	≤ 50/80	≤ 50/80	≤ 80/80	≤ 5/5	≤ 5/10	≤ 5/5	≤ 5/10
Stability (8 hours) ^{4,11} (dB)	± 0.15/± 0.15	± 0.15/± 0.15	± 0.1/± 0.1	± 0.1/± 0.1	± 0.1/± 0.1	± 0.1/± 0.1	± 0.1/± 0.1
FasTesT range (dB)	41	44	39	60	60	60	60
Maximum deviation ⁹ (dB)	± 0.5/± 0.5	± 0.5/± 0.5	± 0.35/± 0.5	± 0.35/± 0.5	± 0.35/± 0.5	± 0.35/± 0.5	± 0.35/± 0.5
ORL range ¹⁰ (dB)	–	–	–	–	–	65	65
ORL uncertainty ^{3,4,10} (dB)	–	–	–	–	–	± 0.4	± 0.4
Talk Set Option⁴	–T02C	–T02BL	–T03BL				
Emitter type	LED	laser	laser				
Wavelength (nm)	1300 ± 25	1310 ± 25	1550 ± 25				
Dynamic range (dB)	30	45	45				
VFL Option⁴							
Emitter type	laser						
Wavelength (nm)	650 ± 10						
Output power (dBm) (typical)	–1						
General specifications							
Size (H x W x D)	22.7 cm x 11.1 cm x 6.4 cm		(8 7/8 in x 4 3/8 in x 2 1/2 in)				
Weight	1 kg		(2.2 lb)				
Temperature	operating		–10 °C to 50 °C (14 °F to 122 °F)				
	storage		–20 °C to 60 °C (–4 °F to 140 °F)				
Storage capacity	512 fibers						
Relative humidity	0 % to 95 % non-condensing						
Power	– NiMH battery 8 hours (for light source and talk set) – 6 hours to fully recharge when unit is off						

Standard accessories

User guide, AC adapter/charger, built-in NiMH batteries, 9 V alkaline battery, shoulder strap, Certificate of Calibration.

Notes

- At 23 °C ± 1 °C with FC/PC connector unless otherwise specified, with an offset nulling for the power meter.
- At 1310 nm for FOT-922, FOT-922X, FOT-923; at 1550 nm for FOT-923X models.
- Resolution, uncertainty and linearity are functions of input power; uncertainty is valid at calibration conditions.
- After a warmup time of 20 minutes.
- At all calibrated wavelengths except 1625 nm.
- When exposed to an input power higher than 28 dBm, uncertainty is valid for a maximum period of 15 minutes.
- Between –30 dBm and 0 dBm; ± 0.15 dB between 0 dBm and 28 dBm; ± 0.3 dB between 28 dBm and 35 dBm (for FOT-923X-P2 only); always referenced at 0 dBm.
- As defined by Telcordia TR-TSY-000887, rms for lasers and FWHM for LEDs.
- Maximum deviation between FasTesT and manual measurement, when loopback/side-by-side reference is taken. Maximum deviation is ± 0.45 dB/± 0.5 dB with Ultra-High-Power power meter models.
- Specifications with FC/APC connector.
- The stability is expressed as ± half the difference between the maximum and minimum values measured during this period.

Ordering Information

FOT-92XXXX-XXXXXX-XXXX-XXXXXXXX-XXXX

Detector

2 = Ge
 2X = GeX
 3 = InGaAs
 3XP1 = InGaAs +28dBm
 3XP2 = InGaAs +35dBm

Power Meter Adapter

FOA-12 = Biconic
 FOA-22 = FC/UPC or FC/APC
 FOA-28 = DIN
 FOA-32 = ST
 FOA-54 = SC/UPC or SC/APC
 FOA-96B = E-2000
 FOA-97 = LX.5
 FOA-98 = LC
 FOA-99 = MU

Source

12C = 850/1300nm LED 50/125
 12D = 850/1300nm LED 62.5/125
 23B = 1310/1550nm LED
 23BL = 1310/1550nm laser
 34BL = 1550/1625nm laser
 BR23BL = 1310/1550nm laser + ORL option
 BR34BL = 1550/1625nm laser + ORL option
 04BL = 1625nm laser
 BR04BL = 1625nm laser + ORL option

Connector

EI-EUI-28 = UPC/DIN 47256
 EI-EUI-76 = UPC/HMS
 EI-EUI-89 = UPC/FC narrow key
 EI-EUI-90 = UPC/ST
 EI-EUI-91 = UPC/SC
 EI-EUI-95 = UPC/E2
 EA-EUI-28 = APC/DIN 47256
 EA-EUI-89 = APC/FC
 EA-EUI-91 = APC/SC
 EA-EUI-95 = APC/E2

Options

T02C = 1300nm LED Talk set
 T02BL = 1310nm Talk set laser
 T03BL = 1550nm Talk set laser
 T02C/VFL = 1300nm LED Talk set + VFL
 T02BL/VFL = 1310nm Talk set laser +VFL
 T03BL/VFL = 1310nm Talk set laser + VFL
 NONE = none

*The type of connector selected on the fastest port will determine the power meter adapter type.

*Other connector adapters available upon request

Example: FOT-9222-BR23BL-EI-EUI-89-T02BL-VFL-EI-EUI-89-FOA-22

Safety


All emitters used for backreflection, FasTest, light source and talk set comply with 21 CFR 1040.10, 1040.11 and IEC 60825-1:1993+A1:1997.

CLASS 1 LASER PRODUCT

CLASS 1 LED PRODUCT for IEC 60825 only

The FOT-920's VFL option is a Class 2 laser product. Actual output power level

may be lower than specified on label. Refer to specifications for output power and wavelength combinations.



CORPORATE HEADQUARTERS	400 Godin Avenue	Vanier (Quebec) G1M 2K2 CANADA	Tel.: 1 418 683-0211 · Fax: 1 418 683-2170
EXFO AMERICA	4275 Kellway Circle, Suite 122	Addison TX 75001 USA	Tel.: 1 800 663-3936 · Fax: 1 972 836-0164
EXFO EUROPE	Le Dynasteur, 10/12 rue Andras Beck	92366 Meudon la Forêt Cedex FRANCE	Tel.: +33.1.40.83.85.85 · Fax: +33.1.40.83.04.42
EXFO ASIA-PACIFIC	151 Chin Swee Road, #03-29 Manhattan House	SINGAPORE 169876	Tel.: +65 6333 8241 · Fax: +65 6333 8242
EXFO CHINA	Beijing New Century Hotel Office Tower, Room 1754-1755 No. 6 Southern Capital Gym Road	Beijing 100044 P. R. China	Tel.: +86 (10) 6849 2738 · Fax: +86 (10) 6849 2662

TOLL-FREE (USA and Canada)

Tel.: 1 800 663-3936

www.exfo.com • info@exfo.com

EXFO is certified ISO 9001 and attests to the quality of these products. EXFO has made every effort to ensure that the information contained in this specification sheet is accurate. However, we accept no responsibility for any errors or omissions, and we reserve the right to modify design, characteristics and products at any time without obligation. Units of measurement in this document conform to SI standards and practices.

Contact EXFO for prices and availability or to obtain the phone number of your local EXFO distributor.
 For the most recent version of this spec sheet, please go to the EXFO website at <http://www.exfo.com/specs>
 In case of discrepancy, the Web version takes precedence over any printed literature.