

Advanced Test Equipment Rentals www.atecorp.com 800-404-ATEC (2832)

Megger.

DLRO 200-115 Digital Low Resistance Ohmmeter

DLRO 200-115 Digital Low Resistance Ohmmeter



- Small and weighs less than 32 lbs (14.5kg)
- Test currents from 10 A to 200 A d.c.
- Filtered direct current output eliminates magnetic transients
- 0.1 μΩ best resolution
- On board memory for up to 300 test results and notes
- RS232 port to download stored results or for real time output to a printer
- Supplied complete with 16 ft. (5m) test leads and download software

DESCRIPTION

The DLRO200-115 is designed to check and measure contact resistance in high voltage circuit breakers, disconnecting switches (isolators), busbar joints, or for any low resistance measurement. The test set accurately measure resistances ranging from $0.1\mu\Omega$ to 1Ω , at high currents.

This versatile instrument can provide test currents from 10 amps up to 200 amps, subject to the load resistance and supply voltage. For those applications that demand a smooth dc current, the DLRO200-115 has extra filtering on the output to reduce mains frequency ripple and can drive 200 amps through a total current loop resistance of

11 milliohms. The filtered output of the DLRO200-115 also eliminates magnetic transients that could inductively trip a breaker's control (bus differential relay), if left in the test circuit.

The unique design allows the weight and size of the DLRO200-115 to be kept to a minimum; the instrument weighs less than 32 lbs. (14.5 kg). This small size plus a water/dust ingress rating of IP54 makes the test set equally at home in the workshop, on the production floor or in the field.

As many as 300 sets of results may be stored in the test set's on-board memory for later download to a PC or may be sent directly to a printer via the RS232 port. You may also add notes to any stored result by using the on-board alphanumeric keypad, thereby making later identification of results easier to determine.

As well as adding notes to stored results, the alphanumeric keypad allows you to set the test current directly by keying in the value required. The DLRO200-115 will check the continuity of the test

circuit, and will quickly ramp the test current up to the desired level. The keyboard is also used to set upper and lower limits for the result and to prevent the use of excessive currents by setting an upper limit to the allowable test current.

The DLRO200-115 uses a four terminal measurement technique to cancel the resistance of the test leads from the measurement.

The test set operates in one of three modes, which are simply selected from the on-screen menu.

CONTINUOUS mode is provided for users who wish to monitor a resistance over a period of time. Connect the test leads, select the test current and press the TEST button. The DLRO200-115 will pass a current continuously, and measure the load resistance at 2 second intervals, until the test button is pressed to stop the test or the test circuit is interrupted.

In NORMAL mode you connect the leads, select the test current and press the TEST button. The test current will ramp up to the desired level, hold for 2 seconds and then ramp down. The whole process takes approximately 10 seconds.

In AUTO mode select the desired current, connect the current leads and press the TEST button. The TEST lamp will flash to show that the DLRO200-115 is ready to carry out a test. As soon as the potential leads are connected, a test will start. To repeat a test, simply break contact with the voltage probes and remake contact.

Measuring individual joints in a busbar is a good example of the convenience to be gained by using AUTO mode. The two current leads are connected to the ends of the busbar. They will remain



Manual, Auto, Continuous.

10 seconds NORMAL /AUTO mode.

connected there until all tests have been completed. When the voltage leads make contact across a joint, the DLRO200-115 detects that all four leads are connected, carries out a test and stops. When you move to the next joint the DLRO200-115 detects the already completed circuit automatically and carries out the next test, and so on until all joints have been tested. The results may be stored automatically and may be recalled to the display or downloaded for review.

Sint, the DIAO200 115 detects	rest nine.	10 seconds NORMAL / AUTO mode.		
ies out a test and stops. When		Refreshed every 2 seconds in CONTINUOUS		
D200-115 detects the already		mode		
arries out the next test, and	Display:	Large, high resolution backlit liquid crystal		
. The results may be stored	display			
the display or downloaded for	Warnings	Current flowing: - LED. Other warnings are		
the display of downloaded for	shown on the lcd display.			
	Data Transfer	Real time or batch download via RS232		
		using Download Manager.		
	Storage Capacity	•		
		300 result sets and memo, battery backed		
		for 10 years.		
	Memo field:	160 characters max.		
	T			
	Test Current			
	Range: Accuracy:	Filtered direct current; 10 A to 200 A d.c. $\pm 2\% \pm 2$ A		
	Voltmeter input			
	impedance:	>200 kΩ		
	Hum rejection:	5 V rms 50 Hz/60 Hz		
		5 V III5 50 II2/00 II2		
	Temperature			
	Operation:	14 to +122° F (-10 to +50° C)		
	Storage:	-13 to 149° F (-25 to +65° C)		
	Calibration:	68° F (20° C)		
	Co-efficient:	<0.05% per ° C		
	Max. Humidity:	95% RH non-condensing		
	Maxi Altitude:	6562 ft. (2000 m)		
er supplied leads)		0002 m (2000 m)		
8 mΩ	Safety:	IEC61010 - (1995)		
4 mΩ	· · · · · ·			
5.4 mΩ	EMC:	EN61326 annex A (heavy industrial)		
6 mΩ				
2	Dimensions:	16.4 x 9.84 x 10.63 in.		
20° C) ambient.		(410 x 250 x 270 mm)		
- 4le1)-	Weight:	31.97 lbs. (14.5 kg) excluding test leads		
othed):				
aload				

Test Modes:

Test Time:

ORDERING INFORMATION

ltem (Qty)	Cat No.	ltem (Qty)	Cat No.
DLRO200-115 High Current Digital Low Resistance Ohmmeter		Optional Accessories at extra cost	
115 V (English QWERTY keyboard)	DLRO200-115 E	16 ft. (5m) Lead set in bag comprising:	6220-755
Included Accessories		2 x 50mm ² current leads with clamps and	
16 ft. (5 m) Lead set comprising 2 x 25 mm ²		2 x potential leads with clips	
current leads with clips and 2 potential		49 ft. (15m) Lead set comprising 2 x 95 mm ²	
		current leads with clamps and	
leads with clips	6220-787	2 x potential leads with clips	6220-757
Download Manager	6111-442	33 ft. (10m) Lead set comprising 2 x 70 mm ²	
User Guide on CD-ROM	6172-763	current leads with clamps and	
RS232 download cable	25955-025	2 x potential leads with clips 6220-750	
Quick Start Guide (English)	6172-782		

UK Archcliffe Road, Dover CT17 9EN England T +44 (0) 1 304 502101 F +44 (0) 1 304 207342 UKsales@megger.com UNITED STATES 4271 Bronze Way Dallas, TX 75237-1019 USA T 1 800 723 2861 (USA only) T +1 214 333 3201 F +1 214 331 7399 USsales@megger.com

OTHER TECHNICAL SALES OFFICES

Valley Forge USA, College Station USA, Sydney AUSTRALIA, Täby SWEDEN, Ontario CANADA, Trappes FRANCE, Oberursel GERMANY, Aargau SWITZERLAND, Kingdom of BAHRAIN, Mumbai INDIA, Johannesburg SOUTH AFRICA, and Chonburi THAILAND Registered to ISO 9001:2000 Reg no. Q 09290 Registered to ISO 14001 Reg no. EMS 61597

DLRO200-115_DS_en_V04

www.megger.com Megger is a registered trademark

SPECIFICATIONS

Measurement:

Range: $0.1 \ \mu\Omega$ to 999.9 m Ω (Subject to supply voltage and leads used)

Accuracy:

Voltage:	$\pm 0.5\% \pm 0.1 \text{ mV}$			
Current:	$\pm 0.5\% \pm$ 0.1 A			
Resistance:	Better than 1% from $100 \ \mu\Omega$ to $100 \ m\Omega$			
Current Lead	Resistance (Megge	r supplied lea		
2 x 16 ft (5 m) 25	mm ² current leads	8 mΩ		
$2 \text{ x 16 ft (5 m) 50 mm}^2 \text{ current leads} 4 \text{ m}\Omega$				
$2 \text{ x } 33 \text{ ft} (10 \text{ m}) 70 \text{ mm}^2 \text{ current leads} 5.4 \text{ m}\Omega$				
$2 \ge 49 \text{ ft} (15 \text{ m}) 95 \text{ mm}^2 \text{ current leads} \qquad 6 \text{ m}\Omega$				

Maximum Continuous Test Time

More than 10 minutes at 200 A @ 68° F (20° C) ambient.

Power Supply

for full output (additional smoothed)

100 to 130 V 50/60 HZ with a load less than 11 m Ω including current leads